




Detectable Silicone Glasses Cord | PE1*GCMB



Product Description

A lightweight and comfortable push-on silicone cord for your spectacles. This circular cord will ensure your eyeglasses are held safely around your neck.

These fully metal detectable silicone glasses cords are manufactured using soft, flexible, silicone rubber containing an evenly dispersed metal detectable

additive with a stainless still clip. The cord is flexible and will push on to most spectacles with ease, once on you can secure with the adjustable metal spring on the adjustable version.

Approximatley 17N of force is required to snap the cord. Please note we recommend customers carry out their own testing and risk assessments.

Detectable Silicone Glasses Cord Advantages

- ✓ Detectable by in-line metal detection systems
- ✓ Highly visible colour for easy visual identification
- ✓ Adjustable and non-adjustable versions available
- ✓ Manufactured from medical grade latex free silicone
- ✓ Displays due diligence in the prevention of foreign body contamination

Product and Packaging Information

Adjustable Cord	PE1AGCMB	Non-Adjustable Cord	PE1GCMB
Colour(s)	Blue	Break Force	Approx. 17N
Pack Weight	0.01kg	Material	Silicone
Pack Size	5	Detectability	Metal Detectable
Cord Length	710mm	Commodity Code	40070000

Safety Certificates / Approvals

BRC Compliant

ISO 9001:2015

Made In Britain

BRC

In
Partnership
with



**MADE IN
BRITAIN**

Fitting Instructions

Grasp the stem of the cord and push onto the arm of the glasses until a secure, comfortable position is obtained.

Metal Detectability

The BST Detectable Glasses Cords are manufactured from metal detectable silicone rubber, with an added stainless steel clip which can be detected by correctly calibrated metal detection systems. The detectability of this product will vary based upon the metal detection systems being used and their calibration. Detectability performance will vary based on, but not limited to the following factors:

- Calibration Levels
- Product Type (E.g. Wet, Dry, Frozen, Liquid)
- Aperture Dimensions
- Orientation

For this reason BST recommend that all our products be thoroughly tested on your metal detection systems by a trained and certified professional. It may be the case that your equipment needs to be re-calibrated in order to reliably detect this product. Such a professional should be available by contacting the manufacturer of your metal detection system.

The information provided in this product specification sheet is based on our experience and knowledge to date and we believe it to be true and reliable. This information is intended as a guide for your use of our products, the use of which is entirely at your own discretion and risk. We, BS Teasdale & Son Ltd, cannot guarantee favourable results and assume no liability in connection with the use of our products. © 2020 BS Teasdale & Son Ltd. All Content, Data & Images are owned by BS Teasdale & Son Ltd and are protected by international copyright law.

BS Teasdale & Son Ltd. Unit 7, Delta Court, Sky Business Park, Robin Hood Airport, Doncaster, South Yorkshire, DN9 3GN

Tel: +44(0)1302 775208 **Email:** sales@bst-detectable.com **Web:** www.bst-detectable.com

Detectable Silicone Glasses Cord | PE1*GCMB | V 1.0 October 2020