



BST Loop Tag Dispensers | ST6LTD*SSMS



The BST Loop Tag Dispensers

Our BST stainless steel loop tag dispensers feature lockable latches and are laser engraved with the BST logo. They can be wall mounted and the front hinged lid is perfect for quick and easy refilling when the rolls are empty. There is also a fill level indicator on

the side to indicate when the roll is close to running out. These dispensers are compatible with the BST large and small loop tags and can be used with the 3mm aluminium spacer dividers which can be bought separately.

BST Loop Tag Dispenser Advantages

- ✓ Detectable by in-line metal detection systems
- ✓ Highly resistant to oxidation & corrosion
- ✓ Easy to wipe clean
- ✓ Strong and highly durable 304 grade stainless steel
- ✓ Can be used as part of HACCP and BRC procedures
- ✓ Displays due diligence in the prevention of foreign body contamination

Product and Packaging Information

Product Code	ST6LTD2SSMS	Dimensions	150 x 250 x 300mm
Weight	2.70kg	Capacity	2 Large / 4 Small Rolls
Product Code	ST6LTD4SSMS	Dimensions	300 x 250 x 300mm
Weight	4.95kg	Capacity	4 Large / 8 Small Rolls
Pack Size	1	Detectability	Metal Detectable
Material	Stainless Steel 304	Commodity Code	73269098

Safety Certificates / Approvals

BRC Compliant	ISO 9001:2015	Made In Britain
---------------	---------------	-----------------



Metal Detectability

The BST dispensers are manufactured from 304 grade stainless steel, as such we would recommend using 304 grade stainless steel test pieces to calibrate your equipment to detect stainless steel contaminants to your specification. Metal detectability performance will vary based on, but not limited to the following factors:

- Calibration Levels
- Product Type (E.g. Wet, Dry, Frozen, Liquid)
- Aperture Dimensions
- Orientation

Orientation is a highly influential factor for the metal detectability of a contaminant that is non spherical, i.e. it will be easier to detect the contaminant when passing in one orientation compared to another - this is known as the orientation effect.

For this reason BST recommend that all our products be thoroughly tested on your metal detection systems by a trained and certified professional. It may be the case that your equipment needs to be re-calibrated in order to reliably detect this product. Such a professional should be available by contacting the manufacturer of your metal detection system.

The information provided in this product specification sheet is based on our experience and knowledge to date and we believe it to be true and reliable. This information is intended as a guide for your use of our products, the use of which is entirely at your own discretion and risk. We, BS Teasdale & Son Ltd, cannot guarantee favourable results and assume no liability in connection with the use of our products. © 2020 BS Teasdale & Son Ltd. All Content, Data & Images are owned by BS Teasdale & Son Ltd and are protected by international copyright law.

BS Teasdale & Son Ltd. Unit 7, Delta Court, Sky Business Park, Robin Hood Airport, Doncaster, South Yorkshire, DN9 3GN
Tel: +44(0)1302 775208 **Email:** sales@bst-detectable.com **Web:** www.bst-detectable.com